

|                   |                       |                                                                                                      |
|-------------------|-----------------------|------------------------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | <b>DATASHEET</b>      |  <b>LAPP GROUP</b> |
|                   | <b>SKINTOP® DIX-M</b> | <b>53350780</b><br><b>14.11.2013</b>                                                                 |


Easy insertion of several cables into one gland  
Higher packing density allows smaller part construction



Automation



Assembly time




Optimum strain relief



Temperature-resistant



UV-resistant



### Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

### Design

SKINTOP® DIX-M VITON® is resistant to oil, water, alkaline solutions, acids, solvents etc.

### Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

### Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

|                             |                 |
|-----------------------------|-----------------|
| Article designation / size: | 50780           |
| Size M:                     | M 50            |
| Number of cables x cable Ø: | 7 x 8           |
| Pieces / PU:                | 10              |
| On request:                 | Special shapes  |
| Colour delivered:           | Black, RAL 9005 |
| Material:                   | NBR<br>VITON®   |
| Protection rating:          | IP 54           |
| Temperature range:          | -40°C to +100°C |

|                    |                          |       |
|--------------------|--------------------------|-------|
| Product Management | Document: SKINTOP® DIX-M | 1 / 1 |
|--------------------|--------------------------|-------|