



► (TC) Standard Bayonet Type
TC-M06-L030-K02.J




Max. operating temperature	: -50 °C / +400 °C
Standard cable types	: Fiber glass + fiber glass + braided wire
Sensor type	: DIN/IEC-584 "J" FeCu-Ni E=J
Protection tube material	: Nickel coated brass
Connector	: Standard 1/4 x 19"

► Technical drawing



Thermoelement Connections



Diameter (M)	: 6 mm
Immersion Length (L)	: 30 mm
Cable length (K)	: 2 meter