

Data Sheet 008



Part Number	K401~K402~k403~K404
Description	On/Off Illuminated Rocker Switch to fit 12mm X 30mm Slot
Design Voltages	12 Volts DC
Maximum Load	16 amps
Contact Resistance	50m Ω max
Insulation Resistance	500 Volts D.C. 100M Ω min
Dielectric Strength	1500 Volts A.C., 1 Minute
Operating Temperature	-25°C ~ +85°C
Electrical Life	10000 Operations

