



## 4-Port Compact KVM Switch

USB, with Cables and Audio Support

Part No.: **151269**

The Manhattan KVM Switch is a four-port compact KVM Switch with audio and mic switching functionality. Its USB support on the console side allows you to use a USB keyboard and mouse. It comes with four sets of detachable USB KVM combo cables and four sets of audio/mic cables for SOHO and office desktop multimedia applications. And it allows you to access, control, boot and reboot four USB-enabled multimedia computers with only one USB keyboard, mouse, monitor and an optional speaker set and microphone.

### Audio and Microphone Switching Offers Uninterrupted Multimedia Experience

The audio and microphone switching function of the KVM Switch allows you to leverage the multimedia systems on each of your two computers. You can monitor the audio/mic input/output of each computer without plugging on and off the audio/mic cables. You can also choose to use either independent/simultaneous switching of both PC channel and audio/microphone channel for their maximum convenience. And it takes only one set of speaker and microphone instead of one set for each computer. Furthermore, it offers you user-programmable simultaneous/independent PC and audio/mic switching functionality for flexible multimedia and KVM switching operation.

### USB Interface Compatibility for Multiplatform Support

The USB interface technology offers multiplatform support for PC, Macintosh G3/G4 and iMac. (The KVM Switching Software client supports only Windows platforms.)

### Zero Cabling Hassles for KVM Users

This KVM Switch saves you cabling troubles with its four 1.5m detachable KVM connection cables. In fact, you have zero cabling troubles since you don't have to worry about finding suitable cables to fit — they come in the package!

### Features:

- Manage/control four USB computers from one keyboard, monitor and mouse
- Audio and microphone switching for uninterrupted multimedia experience across multiple platforms
- Hot-plugging PCs for maintenance without powering down the KVM switch or PCs
- Channel selection via push buttons and keyboard hotkeys
- Supports resolutions up to 1600 x 900 pixels
- LED indicators for easy status monitoring
- USB bus powered: no external power adapter required
- Includes four connection cables for computer, speaker and microphone connection
- Lifetime Warranty

## Specifications:

### Standards

- USB 1.1

### General

- PC connections: 4
- Console connections: 1
- PC port connectors:
  - 4 x USB type A (keyboard, mouse), 4 x 3.5 mm audio jacks (for microphone and speaker sound card connection) and 4 x HD15 male (video) through 4 x 1.8m (6-ft.) connection cables
- Console port connectors:
  - 2 x USB type A (keyboard, mouse)
  - 1 x HD15 female (video)
- Audio connectors:
  - 3.5mm jack (console microphone input)
  - 3.5mm jack (console speaker output)
- Computer selection:
  - Via buttons
  - Via hotkeys
- Video resolution: max. 1600 x 900
- FCC Class B, CE, RoHS

### LEDs

- 1 LED per channel

### Power

- USB bus powered

### Environmental

- Plastic housing
- Dimensions: 125 (L) x 86 (W) x 26 (H) mm (4.9 x 3.5 x 1.0 in.)
- Weight: 0.9 kg (2.0 lbs.)
- Operating temperature: -10 – 50°C (14 – 122°F)
- Operating humidity: 0 – 90% RH, non-condensing
- Storage temperature: -20 – 60°C (-4 – 140°F)

### Package contents

- 4-Port Compact KVM Switch
- Quick installation guide
- PC and audio connection cables (1.8 m / 6 ft.)

