

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

HS-70 HANGING SCALE



VERSION 12/21

Nº 1301359

The hanging scale is intended for precise weighing of items up to a total weight of 100 kg. The scale can be mounted to a sturdy support suitable for the total weight by using a snap hook. The item to be weighed will be attached to the S-shaped hook. The scale is only intended for brief, direct weighing. Dynamic weighing (e.g. bulk measurement) is not permitted and causes measuring errors. The hanging scale is operated by batteries. Power is supplied via two lithium button cells included in the scope of delivery.

HIGHLIGHTS

Strain gauge // Tare function //

Hold function // Automatic shut-off //

TECHNICAL DATA

Power supply	2 x 3 V lithium battery, type CR2032
Weighing range	2 - 100 kg / 4 - 220 lb
Resolution “d”	100 g / 0.2 lb
Tolerance	± 500 g / ± 1.1 lb
Overload display	O-Ld
Unit of weight	kg, lb
Measurement sensor	wear-free strain gauge
Operating conditions	10 to +30 °C, max. 80 % RH
Storage conditions	0 to +55 °C, max. 80 % RH
Dimensions (W x H x D)	70 x 150 x 30 mm
Weight (scale) without accessories	approx. 175 g



PACKAGE CONTENT

Hanging scale // snap hook // S hook // 2 x button cell CR2032 // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.