

KERN ORA 10BA

Refractive index measurement for laboratories and the industry

KERN

Category

Brand	Optics
Product category	Refractometer
Product group	Analogue refractometer
Product family	ORA-B

Measuring System

Measurement temperature [Min] (°C)	10 °C
Measurement temperature [Max] (°C)	30 °C
Measuring method	Light refraction
Measuring range Brix [Min]	0%
Scales	Brix
Measuring ranges	0 % - 10 %
Readabilities [d]	0,1 %
Readout Brix	0,1%
Automatic temperature compensation (ATC)	✓
Appropriate calibration liquid	0 % (distilled water)
Measuring range Brix [Max]	10%
Brix scale	✓
Area of application	Sugar

Construction

Dimension (W×D×H)	198×40×40 mm
Refractometer type	Handheld refractometer
Scale - Display type	Analogue
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

Functions

Automatic temperature compensation	✓
IP protection - complete device	-

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Services (optional)

Article number for factory calibration	961-290
--	---------

Packing & Shipping

Dimensions transport container (W×D×H)	205×75×55 mm
Delivery time	1 d
Dimensions packaging (W×D×H)	215×90×60 mm
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,45 kg
Shipping weight	0,408 kg

Product information

GTIN/EAN number	4045761482623
REACH classification	no prohibited substances

Pictograms

STANDARD

