




GO

Portable Bluetooth speaker



Full-featured, great-sounding, great-value portable speaker.

The JBL GO brings JBL quality sound everywhere. Your all-in-one speaker solution, the GO streams music via Bluetooth from smartphones and tablets, powered by a rechargeable battery with up to 5 hours of playtime. It is also equipped with a convenient noise-cancelling speakerphone, allowing you to pick up calls without turning your speaker off. Available in 8 vibrant colors with a smooth and durable double-injection finishing, the JBL GO provides exciting, eye-catching contrast wherever it goes and easily compliments anyone's style. A built-in strap-hook and optional carrying strap, allows you to bring your music everywhere. In a world where style and audio go hand in hand, the JBL GO is everyone's perfect companion.

Features

- ▶ Wireless Bluetooth streaming
- ▶ Rechargeable battery
- ▶ Speakerphone
- ▶ Great look and feel
- ▶ Audio cable input





Features and Benefits

Wireless Bluetooth streaming

Wirelessly stream high-quality sound from your smartphone or tablet.

Rechargeable battery

Built-in rechargeable Li-ion battery supports up to 5 hours of playtime.

Speakerphone

Take calls from your speaker with a touch of a button – crystal clear thanks to the noise free speakerphone.

Great look and feel

Simplicity of design in 8 vibrant colors.
Integrated carrying strap hook (strap optional).

Audio cable input

Don't worry if there's no Bluetooth, plug the audio cable into the speaker and enjoy your music all the same.

What's in the box:

- 1 x JBL GO
- 1 x Micro USB cable for charging
- 1 x Quick-start Guide
- 1 x Safety sheet

Technical specifications

- Bluetooth version: 4.1
- Support: A2DP V1.2, AVRCP V1.4, HFP V1.6, HSP V1.2
- Transducer: 1 x 40mm
- Output power: 3.0W
- Frequency response: 180Hz – 20kHz
- Signal-to-noise ratio: ≥ 80 dB
- Battery type: Lithium-ion polymer (3.7V, 600mAh)
- Battery charge time: 1.5 hours
- Music playing time: up to 5 hours (varies by volume level and audio content)
- Dimensions (H x W x D): 68.3 x 82.7 x 30.8 (mm)
- Weight: 130g