

---

## Product Feature

---

- One ways of HDMI signal input and output, one ways ARC audio (Toslink) signal output.
- HDMI output port support ARC (audio return channel).
- HDMI supports 4K. Support CEC function.
- Support input and output up to 5metres HDMI standard cable length.
- The device has ARC switch and indicator light to let you know if ARC is disabled or enabled.

---

## Technical data

---

- HDMI resolution support :  
24 / 50 / 60fs / 1080P / 1080i / 720p / 576p / 576i / 480P / 480i, 24 / 30 / 2160P
- Support audio format DTS-HD / Dolby-trueHD / LPCM7.1 / DTS / Dolby-AC3 / DSD
- Support ARC audio output format (relate with display device) LPCM2.0/DTS/Dolby-AC3
- Max transmission width 340MHz
- Max baud rate 10.2Gbps
- Input cable distance  $\leq 5\text{m}$  HDMI standard cable
- Output cable distance  $\leq 5\text{m}$  HDMI standard cable
- Optical fiber cable output distance  $\leq 30\text{m}$ (Use the optical fiber cable loss less the 0.2 dB/m)
- Max working current .15A/5V DC
  
- LED : Green color  
RED color

---

## Standard data

---

- Dimensions approx 53 x 49 x 20mm (l x w x h)
- Weight 70g
- Operating temperature 0 to +40 degree C,
- Operating humidity : 5 to 85%RH (No Condensation)
- Storage temperature -10 to +55 degree C,
- Storage humidity : 0 to 90%RH (No Condensation)
- Operating system support: Windows XP, Windows Vista,Windows 7,Windows 8.....

---

## Delivery Content

- Main Unit x 1
- DC 5.5MM TO USB 2.0 Power Cable x 1
- Manual