

GOAL ZERO YETI[®]400 SOLAR GENERATOR

Wilderness Wall Outlet

Power lights, CPAP machines and TVs anywhere with built-in AC inverters.

Scalable Power

Chainable with other Goal Zero Yeti 400s for longer runtimes.


No Gas Required

Safe for indoor use. Refuel from wall, car or Sun - car charger and solar panel sold separately.




#61209

HOW IT WORKS



WHAT IT POWERS




GOAL ZERO YETI[®]400

SOLAR GENERATOR



*Goal Zero Yeti 400 Solar Generator with 110V AC shown in photo.

- A Charging Port
- B Charging Indicator Light
- C Battery Display
- D 12 Volt Ports
- E USB Ports
- F AC Ports



CHARGE TIME

Wall charger (45W)	5 hours
Car charger (30W)	13 hours
2x Nomad 20	20-40 hours

TECHNICAL SPECIFICATIONS

INPUTS: Charging Port: 14-29V, up to 10A (120W max)

OUTPUTS: 2x 220V AC Unit Inverter (output, 50Hz, pure-sine wave)

Universal or Australia (type 1) AC Plugs: 220V, 1.4A (300W continuous, 600W surge max)

12V Car Port: 12V, up to 10A (120W max)

2x 6mm 12V Ports: 12V, up to 10A (120W max)

2x USB Ports: 5V, up to 2.1A (10.5W max), regulated

Power Pole Chaining Port: 12V, up to 33A (400W max)

pure sine wave

GENERAL: Weight: 29 lbs (13.2 kg)

Dimensions: 10.25 x 8 x 8 in (26 x 20.3 x 20.3 cm)

Chainable

BATTERY: Cell Chemistry: AGM Lead Acid

Pack Capacity: 396Wh (12V, 33Ah)

