

aquapix® W1024 Splash



3m
Waterproof

10MP
Sensor

16MP
Max.
Resolution

4x
Digital
Zoom

6.1cm
2.4"
TFT LCD

VGA
Video
with sound

ISO
800

9 Special
Effects

aquapix®

A brand of Easypix®

Sensor	10 Mega pixel CMOS sensor
Image resolution	16 MP (4608 x 3456) by interpolation 10 MP (3648H x 2736V) 5.0 MP (2592 x 1944) 3.0 MP (2048 x 1536) VGA (640 x 480)
Lens	F/2.8 f = 8.5mm
Focus range	0.5m. ~ Infinity
Macro mode	11cm – 18cm
Digital zoom	4x
Flash strobe	Built-in (Auto / force / off)
LCD display	6.1cm (2.4") TFT color display
White balance	Auto / Daylight / Cloudy / Fluorescent / Tungsten
Video mode	30fps VGA / 30fps QVGA with micro SD card
Ext. memory card	Supports Mico SD cards up to 32GB
File format	Picture: JPEG, Video: AVI
Self timer	10 seconds
PC interface	USB 2.0
Power source	2xAAA alkaline batteries
Language	English / German / Italian / Portuguese / French / Spanish / S-Chinese / T-Chinese
Dimensions	90.3 x 63 x 25.3 mm
Weight	98 g (without batteries)

ACCESSORIES

- USB Cable
- 2 x AAA Batteries
- Hand strap
- Manual
- Pouch
- CD-ROM
- Bundle Software: Arcsoft MediaImpression

W1024 Splash Iceblue Art. Nr. 10012 EAN 4260041682672	W1024 Splash Yellow Art. Nr. 10014 EAN 4260041682726	W1024 Splash Black Art. Nr. 10017 EAN 4260041685109
W1024 Splash Pink Art. Nr. 10013 EAN 4260041682689	W1024 Splash Red Art. Nr. 10016 EAN 4260041685024	W1024 Splash White Art. Nr. 10018 EAN 4260041685093

