


aquapix® W1024 Splash



UP TO **3** METERS
**WATER
PROOF** 



3m
Waterproof

10MP
Sensor

16MP
Max.
Resolution

4x
Digital
Zoom

6.1cm
2.4"
TFT LCD

VGA
Video
with sound

ISO
800

9 Special
Effects

aquapix®
UNDERWATER CAMERAS

Waterproof	Up to 3 meters
Sensor	10MP CMOS sensor
Image resolution	16MP (4608x3456) by interpolation 10MP (3648x2736), 5.0MP (2592x1944) 3.0MP (2048x1536), VGA (640x480)
Lens	F/2.8 f = 8.5mm
Focus range	0.5m. ~ infinity
Macro mode	11cm - 18cm
Digital zoom	4x
Flash mode	Auto / force / off
Display	6.1cm (2.4") TFT color display
White balance	Auto / Daylight / Cloudy / Fluorescent / Tungsten
Video mode	30fps VGA / 30fps QVGA with micro SD card
External memory	Supports Mico SD cards up to 32GB (not included)
File format	Picture: JPEG, Video: AVI
Self-timer	10 seconds
PC interface	USB 2.0
Power source	2xAAA alkaline batteries
OSD languages	English / German / Italian / Portuguese / French / Spanish / S-Chinese / T-Chinese
Dimensions	90.3 x 63 x 25.3 mm
Weight	98g (without batteries)

ACCESSORIES

- USB cable
- 2x AAA batteries
- Hand strap
- Manual
- Pouch
- CD-ROM
Bundle Software: Arcsoft MediaImpression



W1024 Splash Iceblue
Art. Nr. 10012
EAN 4260041682672

W1024 Splash Yellow
Art. Nr. 10014
EAN 4260041682726

W1024 Splash Black
Art. Nr. 10017
EAN 4260041685109

W1024 Splash Pink
Art. Nr. 10013
EAN 4260041682689

W1024 Splash Red
Art. Nr. 10016
EAN 4260041685024

W1024 Splash White
Art. Nr. 10018
EAN 4260041685093

