



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

SPAS-4800/4 USB CHARGER

Nº 1362464

CE

VERSION 01/16

This USB charger features 4 USB outputs, which can deliver an output current of max. 2400 mA each (max. 4800 mA total). These high-current outputs can be used for devices which feature a quick-charge function, such as the iPad®. Power is supplied via a normal household power outlet.

HIGHLIGHTS

Auto-detect function for optimal charging control //

4 USB charging ports with max. 2400 mA each //

Total output current 4800 mA //

Output voltage 5 V/DC //

Overload protection //

Short-circuit proof //

Blue status LED //



TECHNICAL DATA

Input voltage	100 – 240 V/AC, 50/60 Hz
Output voltage	5 V/DC
Output current	4800 mA (total) 1 x max. 2400 mA 2 x max. 2400 mA 3 x max. 1600 mA 4 x max. 1200 mA
Output power	max. 24 W
Operating conditions	0 to +35 °C, 20 – 85 % RH (non-condensing)
Storage conditions	-20 to +60 °C, 10 – 90 % RH (non-condensing)
Dimensions (W x H x D)	35 x 70 x 110 mm
Weight	140 g

PACKAGE CONTENT

USB charger // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.