



Einhell

TH-AC 190/6 OF Air compressor

Art.-No. 40.204.95

Features

- Transport handle (1)
- Pressure gauge (2) and quick coupling (3) for regulated working pressure
- Pressure controller (4)
- Base foot with vacuum cup function (5)
- Drain valve (6)
- Safety valve (7)
- Well accessible on / off switch (8)
- Cable reel (9)
- Oil-free and thus low-maintenance
- 10 years warranty against rusting through of the tank



9

Technical Data

- | | |
|---------------------------|---|
| ■ Mains connection: | 230 V ~ 50 Hz |
| ■ Motor rating: | 1.1 kW; S3 25% |
| ■ Intake capacity: | 185 l / min |
| ■ Output power: | with 0 bar: 139 l / min
with 4 bar: 77 l / min
with 7 bar: 60 l / min |
| ■ Tank capacity (liters): | 6 l |
| ■ Speed (Pump): | 3,550 rpm |
| ■ Operating pressure: | max. 8 bar |
| ■ No. of cylinders: | 1 |
| ■ Product weight: | 9.2 kg |

Logistic Data

- | | |
|-----------------------|--------------------|
| ■ Net weight: | 9.2 kg |
| ■ Gross weight: | 10.6 kg |
| ■ Packing dimensions: | 352 x 312 x 365 mm |
| ■ Bar code: | 4006825 592184 |
| ■ Sales Unit: | 1 pc |

