



DATASHEET

YV Jumper Wire 2x0.2 mm² 25meter

Version 12/15

Item no. 1386658(White/Brown) 1386663(White/Red)
1386659(Red/Blue) 1386664(White/Black)
1386660(White/Green) 1386665(White/Pink)
1386661(White/Yellow) 1386666(Black/Red)
1386662(White/Blue) 1386667(Red/Green)

Jacket, outer dimension.....PVC 2 x 0.9mm
No. of conductors.....2 x 0.5mm
Strand per conductor.....0.2 sqmm
Length.....25 meter
Conductor materialcopper
Insulation resistance..... Min 200M ohm x km
Conductor resistance..... Max 110 ohm/KM
Maximum dielectric strength..... 800V / AC
Operating temperature range..... -20 to +70 ° C
Rated voltage.....< AC 50V / DC 75V
Rated current.....1.6A
Storage temperature range..... -20 to +70 ° C
Operating humidity range..... 35%~95%
Storage humidity range..... 35%~95%



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2013 by Conrad Electronic SE.