

DATASHEET**Alarm Cable 20 x 7 x 0.2 mm²****Version 9/15****Item no.: 93030c492**

| | |
|------------------------------------|----------------------|
| Jacket, outer dimension..... | PVC 8.1 mm |
| Cross section area..... | 20 x 0.22 sqmm |
| CCA Strand per conductor..... | 7 x 0.2 mm |
| Color..... | white |
| AWG..... | 26AWG |
| Packaging..... | 50 meter spool |
| Dielectric strength..... | 200M ohm KM |
| Material of the fine wire..... | CCA |
| Conductor resistance | 160ohm/KM |
| Operation Voltage..... | < AC 50V / DC 75V |
| Conductor resistance (Ohm/km)..... | Max 57.5 ohm/m |
| Insulation resistance..... | Min 200M ohm x km |
| Rated voltage..... | < AC 50V / DC 75V |
| Temperature range..... | min. -20°C max. 70°C |