

### Americas

Atlanta - 678-957-9614  
Austin - 512-257-3370  
Boston - 774-760-0087  
Chicago - 630-285-0071  
Cleveland - 216-447-0464  
Dallas - 972-818-7423  
Detroit - 248-848-4000  
Houston - 281-894-5983  
Indianapolis - 317-773-8323  
Los Angeles - 949-462-9523  
New York - 631-435-6000  
Phoenix - 480-792-7200  
Santa Clara - 408-961-6444  
Toronto - 905-673-0699

### Europe

Austria - Wels - 43-7242-2244-39  
Denmark - Copenhagen - 45-4450-2828  
France - Paris - 33-1-69-53-63-20  
Germany - Munich - 49-89-627-144-0  
Italy - Milan - 39-0331-742611  
Netherlands - Drunen - 31-416-690399  
Spain - Madrid - 34-91-708-08-90  
UK - Wokingham - 44-118-921-5869

### Asia/Pacific

Australia - Sydney - 61-2-9868-6733  
China - Beijing - 86-10-8569-2100  
China - Chengdu - 86-28-8665-5511

### Asia/Pacific (Continued)

China - Chengdu - 86-28-8665-5511  
China - Chongqing - 86-23-8980-9588  
China - Dongguan - 86-769-8702-9880  
China - Hangzhou - 86-571-8792-8115  
China - Hong Kong SAR - 852-2943-5100  
China - Nanjing - 86-25-8473-2460  
China - Qingdao - 86-532-8502-7355  
China - Shanghai - 86-21-5407-5533  
China - Shenyang - 86-24-2334-2829  
China - Shenzhen - 86-755-8864-2200  
China - Wuhan - 86-27-5980-5300  
China - Xiamen - 86-592-2388138  
China - Xian - 86-29-8833-7252  
China - Zhuhai - 86-756-3210040  
India - Bangalore - 91-80-3090-4444  
India - New Delhi - 91-11-4160-8631  
India - Pune - 91-20-3019-1500  
Japan - Osaka - 81-6-6152-7160  
Japan - Tokyo - 81-3-6880-3770  
Korea - Daegu - 82-53-744-4301  
Korea - Seoul - 82-2-554-7200  
Malaysia - Kuala Lumpur - 60-3-6201-9857  
Malaysia - Penang - 60-4-227-8870  
Philippines - Manila - 63-2-634-9065  
Singapore - 65-6334-8870  
Taiwan - Hsin Chu - 886-3-5778-366  
Taiwan - Kaohsiung - 886-7-213-7828  
Taiwan - Taipei - 886-2-2508-8600  
Thailand - Bangkok - 66-2-694-1351

01/27/15



Microchip Technology Inc. • 2355 West Chandler Blvd. • Chandler, AZ 85224-6199

[www.microchip.com](http://www.microchip.com)

The Microchip name and logo, the Microchip logo, and MPLAB are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries. All other trademarks mentioned herein are property of their respective companies. © 2015, Microchip Technology Incorporated, Printed in the U.S.A. All Rights Reserved. 05/15

DS40001791A

## Overview

The Curiosity Development Board layout and schematic can be found on the Microchip web site:

[www.microchip.com/curiosity](http://www.microchip.com/curiosity)

This board provides flexibility for experimentation through an application header with ground (GND) and supply voltage (VDD) connections. It also includes a set of indication LEDs, mTouch<sup>®</sup> button and push-button switches, and a variable potentiometer. Additionally, it features a Bluetooth module footprint and a mikroBUS<sup>™</sup> header to accommodate a variety of plug-in Click<sup>™</sup> Boards that can be used in application development. Curiosity is fully compatible with MPLAB<sup>®</sup> Code Configurator and MPLAB X v3.05 or later.

**Note:** Low Voltage Programming (LVP) must be enabled in MPLAB X.

## Board Power-Up

Power is supplied by the USB connector (J2) on the back of the board.

## Demonstration Program

After applying power to the Curiosity Development Board via the USB connector J2 on the backside of the board, LED (D7) will automatically turn on. Turn POT1 clockwise to increase the brightness of the LED (D7) and counterclockwise to decrease its brightness. Press the push button (S1) to turn on LED (D4) and touch the mTouch button (S3) to turn on LED D6.

## Board Layout

The Curiosity Development Board is shown in [Figure 1](#). A PIC16F1619 20-pin microcontroller is populated in the center of the demo board next to the identification label U4. The Curiosity Development Board can also accommodate 14- and 8-pin, 8-bit microcontrollers in the same socket (U4). The PIC16F1619 is initially connected to the following components:

- Push Button (S1)
- Potentiometer (POT1)
- Master Clear Reset Button (S2)
- mTouch Button (S3)
- LEDs (D4 – D7)
- mikroBUS Header (J35, not populated)
- RN4020 Bluetooth Module Footprint (U6, not populated)

The board is flexible and allows individual experiments. A power and ground header (J7), as well as isolation headers (J39, J40, J3 – J6 and J13) are provided to expand the flexibility of the Curiosity Development Board.

FIGURE 1: CURIOSITY DEVELOPMENT BOARD LAYOUT

