



PIN OUT

P1	P2
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHELL	SHELL (DRAIN WIRE)

**NOTE:**

1. Electrical test:
  - (1). 100% open short & miss wire test;
2. RoHS 2.0 and REACH COMPLIANT
3. MARKING: COMPUTER INTERFACE CABLE 30V 80°
4. PACKING: 1PCS/INLINE BAG+LABEL, 10PCS/PE BAG+LABEL

**MATERIAL LIST:**

⑤	MOLDED	BEIGE PVC RAL7038	2	
④	SCREW	#4-40 THUMB SCREW, NICKEL PLATED	4	
③	DB 9PIN FEMALE	SOLDER TYPE, BLUE INSULATION, GOLD FLASH CONTCATS, NICKEL PLATED SHELL	1	
②	DB 9PIN MALE	SOLDER TYPE, BLUE INSULATION, GOLD FLASH CONTCATS, NICKEL PLATED SHELL	1	
①	CABLE	[28AWG (7*0.12 BC)*9C, AL-FOIL SHIELDED WITH A DRAIN WIRE (7/0.12 TC) PVC JACKET] Beige RAL7038 OD=∅5.4±0.2MM	1	
NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK

					PRODUCT NAME	DB9 MALE TO FEMALE		UNIT	MM	
NEW					2015. 11. 10	A	DRAWNBY	CHECKBY	APPOBY	DATE
BY	CHK	REVISION RECORD MODIFICATIONS			DATE	REV.	Alvan	Alvan		2015. 11. 10