


Technical requirement:

1. The product should be followed with Cat 6 connection and technical standard;
2. Unmarked tolerance dimension on the basis of SJ/T10628 - 1995 6 grade;
3. ROHS2.0 ADN REACH COMPLIANT
4. Operation temperature:-10°C ~ +60°C
Storage temperature:-40°C ~ +70°C
Operation humidity:30%~80%
Storage humidity:30%~80%
5. PACKING: 1PCS/Renkforce color box (SIZE:105 x 20 x 140mm)

Connection Method



MATERIAL LIST:

⑥	Contact	8P8C 3U" Gold Plated	8	
⑤	Base	ABS	1	
④	roof cover	ABS	1	
③	shielded enclosure	Nickel Plated brass t=0.3mm	2	
②	PCB	FR-4, t=0.8	1	
①	PCB outlet	PBT	2	

NO	MAT. NAME	DESCRIPTION	QT' Y	REMARK
BY	CHK	REVISION RECORD MODIFICATIONS		

			ITEM NO.	1404063		
		PRODUCT NAME	CAT.6 STP Coupler	UNO ITEM NO.	276200	UNIT MM
		DATE	2015. 12. 21	DRAWNBY	CHECKBY	APPOBY
		REV.	FERGUS			DATE
						2015. 12. 21