

- Product Data Sheet -



Article **Competition 4AAA LED - Flashlight**

Art. number	LX0435AAA	Color	Black	Recom. Retail Price	25,95 €
Manufacturer	LiteXpress	Material	Aluminum		



Description: Stray light on the trail, concert or workshop? With the LX0435AAA Competition by LiteXpress you will definitely have a sensationally bright LED flashlight. With a beam range of 280 meters, no task remains unsettled. Due to the aluminum housing - paired with the high-quality splash water protection, the lamp is also extremely resistant and can be operated by the end cap switch with one hand. Whether in the assembly hall, in the dark forest or in your houses cellar: This flashlight always makes a good and above all BRIGHT figure! The lamp has an end cap switch. Included in delivery is a pocket clip and 4 AAA alkaline batteries.

Features - Insulation Products

Insulation effect		Sealing		Capacity	
Cold in hours	n/a	Type of lid	n/a	Capacity in liters	n/a
Hot in hours	n/a	Filling hole in cm	n/a		

Specials

Features - Flashlights

Battery/Rech. Battery		Brightness		Other	
Type	AAA	Max lumens	420	Light source	LED
Amount required	4	Min lumens	1	Amount of modes	2
Weight battery in gr	11,00			Modes / functions	High, Low
Total weight in gr	44,00	Luminous range			
Batteries included?	yes	Max meters	280	Special features	
		Min meters	20		
		Lighting duration			
		Max ¹ h	1,8		
		Min ¹ h	70,0		

¹ Max relates to the lighting duration in highest light mode and Min to the duration in lowest light mode

Dimensions / Others

Inner Carton		Product		Other	
Length in cm	15,70	Length in cm	4,20	Country of Origin	China
Width in cm	25,30	Width in cm	4,20	Customs tariff num.	8513100000
Height in cm	25,80	Height in cm	14,60	EAN13 number	4895168100206
Weight in gr	1,72	Diameter	-		
Units	6	Weight in gr	181,00		
Outer Carton		Product packaging		Information - Multitools / Knives	
Length in cm	32,50	Length in cm	4,30	Total length in cm	n/a
Width in cm	53,00	Width in cm	13,60	Handle length in cm	n/a
Height in cm	54,30	Height in cm	24,30	Blade length in cm	n/a
Weight in gr	14,58	Weight in gr	0,27	Tools included	n/a
Units	48	Units	1		