

# DATASHEET


## RJ45 CAT5 8/8 Panel Jack

Front: Female


Back: Male with 60cm cable,  $\Phi$  22mm

Version 12/15

Item no.: 1408770 – Silver  
1408771 – Black



10MAX: means the panel thickness, the max thickness for the panel no more than 10mm.



Specification .....	Front: RJ45 Female Back: RJ45 Male with 60cm cable
Cable Standard.....	T568B
Mounting diameter.....	22 mm
Panel Thickness.....	1~10 mm
Body Material.....	Aluminium anodized (Silver color)
Transmission Rate .....	$\geq 30$ MB/s
Operating Temperature.....	-25°C ~ +55°C (NO-Freezing)
Operating Humidity.....	45~85%RH(NO Condensation)