

DATASHEET

6.35mm Plug, mono,right angle

Version 01/16

Item no. 1408837



Color.....	Grey
No. of pins.....	3
Audio Channel.....	Stereo
Contact plated.....	Nickel
Connection.....	Soldering
Category.....	6.35 mm,
Connector type.....	Plug,right angle
Mating cycles.....	> 3000
Dimension.....	53.8*46*14.4 mm
Tolerance.....	±1 mm
Contact resistance.....	≤ 10 m Ω
Withstand voltage.....	0.5kV dc
Material and plated.....	zinc alloy/ nickel plating
Cable diameter can be used.....	3.5-8.0 mm
Operation temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%
Storage temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%