

## DATASHEET

6.35mm Plug, mono, gold plated

Version 01/16

Item no. 1408840



|   |   |
|---|---|
| Color.....                              | black   |
| No. of pins.....                        | 2   |
| Audio Channel.....                      | mono  |
| Contact plated.....                     | Gold  |
| Connection.....                         | Soldering   |
| Category.....                           | 6.35mm, gold plated                                   |
| Connector type.....                     | Plug, straight  |
| Mating cycles.....                      | > 3000  |
| Dimension.....                          | Ø 14.4 x 75.4(H) mm                                   |
| Tolerance.....                          | ±1 mm   |
| Contact resistance.....                 | ≤ 10 mΩ   |
| Withstand voltage.....                  | 0.5kV dc  |
| Material and plated.....                | zinc alloy/ gold plating                              |
| Cable diameter can be used.....         | 3.5-8.0 mm  |
| Operation temperature and humidity..... | -25 degree Celsius to<br>+80 degree Celsius / 10%-90% |
| Storage temperature and humidity.....   | -25 degree Celsius to<br>+80 degree Celsius / 10%-90% |