



DATASHEET

Universal Relay 24 VDC 30 A 4 Pins BN 1433304

Version 07/16



Pins.....	4
Outline Dimension.....	32.2 * 27.6 * 28 mm
Contact form.....	1a
Contact form (resistance).....	30 A 240 VAC / 28 VDC
Coil voltage (DC).....	24 V
Coil power (DC).....	0.9 W
Close voltage	≤ 75% V
Release voltage	≥ 10% V
Strength between Contacts	1,500 VAC / min
Strength Contacts and coils	2,000 VAC / min
Contact resistance	≤ 50 mΩ
Insulation resistance	≥ 1,000 mΩ
Ambient temperature	-55 - 85 Celsius degree.
Mechanical life	10,000,000 times / OPC
Electrical life	100,000 times / OPC
Mounting form	PCB, Fasten
Weight	0.03 KG
Application.....	Meter ,Water Heater
Operation temperature and humidity.....	- 55 ~ 85 degree Celsius ; 35 % ~ 85 % RH
Storage temperature and humidity	0 ~ 85 degree Celsius ; 35 % ~ 80% RH
Dimension drawing with tolerance	Out dimension ≤ 1 mm, Tolerance: ± 0.2 mm; ≤ 1~5 mm, Tolerance: ± 0.3 mm Out dimension > 5 mm, Tolerance: ± 0.4 mm
Tolerance of mounting hole.....	± 0.1 mm

Distributed by Conrad Electronic SE

This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2016 by Conrad Electronic SE.