

File No.	Length(mm)	Weight(g)	Packing
29212c101	500+60/-0	17	VP1: 10.5 x 14 cm (depth : 2)
29212c101a	1000+60/-0	35	VP1: 10.5 x 14 cm (depth : 3)
29212c101b	3000+100/-0	100	VP2: 10.5 x 24 cm (depth: 3.5)
29212c101c	5000+100/-0	165	VP2: 10.5 x 24 cm (depth: 3.5)

MATERIAL LIST

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
⑤	CONNECTOR	RJ45 8P8C'S SHIELDED ,PIN GOLD PLATED 3u"	1PCS	
③④	OVER MOLD	PVC	1PCS	
②	CONNECTOR	RJ45 8P8C'S SHIELDED THE SHELL PLATED NICKEL, PIN GOLD PLATED 3u" ,TRANSPARENT	1PCS	
①	CABLE	Cat.5e F-UTP (26AWG BC-1P)*4+AL-FOIL+Jacket: PVC OD:5.9±0.2MM	1PC	

NOTE:

- 1.ELECTRICAL TEST:100% OPEN SHORT & MISS WIRE TEST;
- 2.RoHS 2.0 and REACH Compliant
- 3.printing: CAT.5E F/UTP PVC 100MHz ISO/IEC 11801 & EN50173-1 &ANSI/TIA-568-C.2
4. OPERATING TEMPERATURE:-10°C ~ 60°C
OPERATION HUMIDITY:30% ~ 85%
STORAGE TEMPERATURE:-20°C ~ 75°C
STORAGE HUMIDITY:30% ~ 90%

					CUSTOMER NO.		CEI Conrad Electronic International (HK) Ltd		ITEM NO.	
					PRODUCT NAME	CAT 5E F/UTP Extended Patch cord	REF. NO.		UNTT	MM
NEW					2016-03-03	A	DRAWNBY	CHECKBY	APPOBY	DATE
BY	CHK	REVISION RECORD MODIFICATIONS			DATE	REV.	ARVIN	ALVAN		2016-03-03



Cable ID: CAT5E-F/UTP



Date / Time: 03/07/2016 01:46:30 PM
Test Limit: ISO11801 Channel Class D
 Cable Type: Cat 5e F/UTP
 NVP: 76.0%

Operator: ALVAN
 Software Version: 2.7700
 Limits Version: 1.9400
 Calibration Date:
 Main (Tester): 09/22/2013
 Remote (Tester): 09/22/2013

Test Summary: PASS

Model: DTX-1800
 Main S/N: 1247071
 Remote S/N: 1247072
 Main Adapter: DTX-CHA002
 Remote Adapter: DTX-CHA002

Length (ft)		N/A
Prop. Delay (ns)	[Pair 36]	14
Delay Skew (ns)	[Pair 36]	1
Resistance (ohms)		N/A



Compliant Network Standards:
 10BASE-T 100BASE-TX 100BASE-T4
 1000BASE-T 10GBASE-T ATM-25
 ATM-51 ATM-155 100VG-AnyLan
 TR-4 TR-16 Active TR-16 Passive