

Model No.:CS-351-15-24V


1.Basic Condition

- 2.1 Rated Voltage:24VDC
- 2.2 Operating Voltage:20~28VDC
- 2.3 Output Power:15W
- 2.4 Operating Temperature Range :-20°C~+70°C
- 2.5 Storage Temperature Range:-30°C~+85°C


2.Electrical Characteristics

- 3.1 Sound Press Level: 115+3dB at 100cm / 24VDC
- 3.2 Consumption Current:350 mA
- 3.3 Coil Impedance:14Ω±3
- 3.4 Tone Nature: One Tone
- 3.5 Material: ABS Plastic

3.Measuring Method



4.Sound Press Level



5.Product Photo & Dimension

