

# Model No.:CS-401-15-24V


## 1.Basic Condition

- 1.1 Rated Voltage:24VDC
- 1.2 Operating Voltage:20~28VDC
- 1.3 Output Power:15W
- 1.4 Operating Temperature Range :-20°C~+70°C
- 1.5 Storage Temperature Range:-30°C~+85°C


## 2.Electrical Characteristics

- 2.1 Sound Press Level: 115+3dB at 100cm / 24VDC
- 2.2 Consumption Current:350 mA
- 2.3 Coil Impedance:14Ω±3
- 2.4 Tone Nature: One Tone
- 2.5 Material: ABS Plastic

## 3.Measuring Method



## 4.Sound Press Level



## 5.Product Photo & Dimension

