


**Apple Lightning USB Sync- & Ladekabel**

- Anschlüsse: Apple Lightning-Stecker (8 Pin)  
USB 2.0 Stecker (Typ A)
- max. Datenrate: 0,48 Gbit/s
- Knickschutz: beidseitig
- Kabel: Rundkabel; L: 1,0 m
- Gewicht: 22 g
- Konformität: EMV, RoHS

**Apple Lightning USB Sync & Charging Cable**

- Connections: Apple Lightning plug (8 pin)  
USB 2.0 socket (type A)
- max. data rate: 0.48 Gbit/s
- Kink protection: both sides
- Cable: round cable; L: 1.0 m
- Weight: 22 g
- Conformity: EMC, RoHS

**Änderungen**

Datum	Name	gez.:	Datum	Name	Bezeichnung	Blatt
		gez.:	05.08.2016	tf	DAT Lightning 1,0m(weiss) PL 	
		gepr.:	05.08.2016	tf		
		Norm:			Zeichnungs-Nr.:	von
Änderungen vorbehalten / Subject to change					54600	