

Data Sheet

USC14TR-40MPW 1 pc(s)



Technical data

Center Frequency (KHz): 40 ± 10

Capacitance (pF): $1800 \pm 20\%$ at 1000Hz

Transmitting Sound Pressure Level (dB): ≥ 85 (10cm/9Vrms Sine Wave)

Transmitting Sound Pressure Level (dB): ≥ -65 (10cm/9Vrms Sine Wave)

-6 dB Directivity (deg) : $60 \pm 10^\circ$

Ringing: ≤ 1.3 ms

Allowable Input Voltage (V p-p): 120

Operation Temperature (°C): $\leq 70^\circ\text{C}$

Terminal: PIN

Weight (g): 4.5

Data Sheet

Drawing

External Dimension Drawing(mm):

