

**BORN TO EXCEED**  
**armyTek**®



- ◆ Canadian manufacturer
- ◆ Designed especially for your needs
- ◆ Components by USA and Japan



TACTICAL LIGHTS



## Predator PRO v3

1700 LED lumens • 451 meters

### Extreme Beam Distance

Due to Long-Range Optics Technology even with a compact-size reflector your target is detectable at 451 meters distance. Distinct hotspot and minimal spill guarantee directed aim illumination. New Cree XHP35 High intensity LED provides impressive brightness 1700 LED lumens.

### Constant Ultra bright Light

Due to FLAT Runtime Technology the brightness remains constant even in -25°C frost and with almost discharged batteries. Even in Turbo mode the brightness is the same for the whole operation time.

### Designed for Weapon Mounting

Standard 1" body diameter matches up with most weapon mounts. Reliable body, red/green/blue filters and original remote switches for comfortable Hunting and secure Military application. No failures while shooting.

### Light-weight, durable & waterproof

Made of aircraft-grade aluminium using the Slim Profile Technology in combination with functional ergonomic design. Guaranteed durability — stands up the recoil of any gun gauge and falling from 30 meters height. The flashlight works for more than 5 hours at 50 meters depth.

### Up to 100 days of Constant Light

Record runtime with 1x18650 Li-Ion battery due to the Firefly Technology. Compatible both with rechargeable 18650 Li-Ion and non-rechargeable CR123A batteries.



## Dobermann

1700 LED lumens • 395 meters

### Bright and focused light

Marvelous brightness 1700 lumens and special optics to ensure narrow and centered light for aiming at the distance up to 395 m.

### Highly reliable

The highest standards of durability; solid-state construction and efficient protection of internal components guarantee no-break work of the flashlight - it stands up to recoil of 12 gauge shotgun and falling from 30 meters.

### Cost effective tactical flashlight

Outstanding light characteristics, robust construction and tested quality at available price for those who need simple in use and truly reliable underbarrel flashlight. Compatible with additional original accessories for underbarrel application: remote switches, mounts for different types of weapon.

### Easy to carry and operate

Compact size and light weight perfectly suit for using on the weapon. Steel bezels protect the elements of construction from fallings and impacts. Several brightness modes for multipurpose use in different situations and simple user-interface for comfortable one-hand operation of the flashlight.

### Up to 18 days of operation with one battery

Record runtimes: on one battery flashlight will work for 1 hour in Turbo mode and up to 200 days in Firefly mode.

Armytek Optoelectronics Inc.

13-85 West Wilmot St, Richmond Hill  
Ontario, L4B 1K7, Canada

Phone: +1 (905) 597-7478  
[www.armytek.com](http://www.armytek.com)



Model	Predator Pro v3	Predator v3	Viking Pro v3	Viking v3	Dobermann Pro	Dobermann Green	Dobermann Red
<b>Field of application</b>	Hunting with rifles, Underwater Hunting, Military, Fishing, Survival	Hunting with rifles, Underwater Hunting, Military, Fishing, Survival	Hunting with shotguns, Military, Fishing, Cycling, Outdoor activities	Hunting with shotguns, Military, Fishing, Cycling, Outdoor activities	Hunting with shotguns, Military, Fishing, Cycling, Outdoor activities	Hunting with shotguns, Military	Hunting with shotguns, Military
<b>Light output, LED / OTF lm*</b>	1700 / 1400	1200 / 1000	2300 / 1800	1250 / 1050	1700 / 1400	240 / 200	200 / 160
<b>Beam distance*</b>	451 m	437 m	286 m	366 m	395 m	274 m	212 m
<b>Hotspot / Spill</b>	5°:40°	5°:40°	10°:80°	5°:40°	5°:40°	5°:40°	5°:40°
<b>Water resistance</b>	Submersion up to 50 meters, more than 2 hours						
<b>Pick beam intensity, cd</b>	50750	47750	20500	34200	39000	18750	11250
<b>Light tint</b>	Cool white / Warm	Cool white / Warm	Cool white / Warm	Cool white / Warm	Cool white / Warm	Green	Red
<b>Brightness stabilization</b>	FULL (constant light)	DIGITAL	FULL (constant light)	DIGITAL	FULL (constant light)	FULL (constant light)	FULL (constant light)
<b>LED</b>	Cree XHP35 HI	Cree XP-L HI	Cree XHP50	Cree XP-L	Cree XHP35 HI	Cree XP-E2	Cree XP-E2
<b>Number of modes</b>	9	6	9	6	9	6	6
<b>Modes / Runtimes</b>	0.35 lm / 100 days 1.7 lm / 18 days 28 lm / 36 h 170 lm / 8.5 h 370 lm / 3.5 h 670 lm / 1.8 h 1000 lm / 1.3 h 2 Strobe	1.7 lm / 18 days 28 lm / 48 h 170 lm / 9 h 370 lm / 3.8 h 1000 lm / 1.5 h Strobe	0.4 lm / 200 days 2.5 lm / 40 days 30 lm / 50 h 165 lm / 10.5 h 390 lm / 4 h 900 lm / 1.7 h 1800 lm / 1 h 2 Strobe	2.5 lm / 18 days 32 lm / 48 h 190 lm / 9 h 410 lm / 3.8 h 1050 lm / 1.5 h Strobe	0.15 lm / 200 days 1.7 lm / 40 days 30 lm / 50 h 150 lm / 10.5 h 350 lm / 4 h 800 lm / 1.7 h 1400 lm / 1 h 2 Strobe	1.7 lm / 18 days 32 lm / 48 h 75 lm / 19 h 120 lm / 7 h 200 lm / 4 h Strobe	0.8 lm / 18 days 12 lm / 48 h 40 lm / 19 h 75 lm / 7 h 160 lm / 4 h Strobe
<b>Power source</b>	1 x 18650 Li-Ion / 2 x 18350 Li-Ion / 2 x RCR123 Li-Ion / 2 x CR123A						
<b>Length</b>	154 mm		154 mm		140 mm		
<b>Head diameter</b>	41 mm		41 mm		34 mm		
<b>Body diameter</b>	25.4 mm		25.4 mm		25.4 mm		
<b>Weight (without batteries)</b>	135 g		126 g		115 g		
<b>Package Set</b>	Holster, rubber grip, removable clip, lanyard, 2 spare O-rings, 2 rubber rings, rubber button, manual						

\* Light outputs for flashlights with Warm light are about 7% less, beam distances are about 3% less.