


# **ASSNET250 Category 6 U-UTP Twisted Pair Installation Cable**




- Category 6 Compliant, ISO/IEC 11801, DIN EN 50173, DIN EN 50288-5-1
- √ Stress less paper pullout box
- √ assures best performence

### **Abstract**

ASSNET250 CAT 6 U-UTP installation cable, raw, Length 305 M, Paper Box, AWG 23/1, PVC Color grey

#### **Features**

- PVC outer sheath
- · Stress less paper pullout box
- Category 6 Compliant, ISO/IEC 11801, DIN EN 50173, DIN EN 50288-5-1
- AWG 23 conductor
- 250 MHz



#### **Product Overview**

ASSNET Category 6 U-UTP installation cables are manufactured and tested to the ISO/IEC 11801, DIN EN 50173 and DIN EN 50288-5-1 Category 6 specifications. Every cord consists of 8 color coded AWG 23 polyethylene insulated conductors. The conductors are twisted together to form 4 pairs with varying lay lengths.

Printing details along the outer sheath includes the brand name, item code and cable length 0 - 305 meter. The cable is packed in a paper pullout box which makes the installation easy. Moreover it is reducing waste.

#### **Part Number Information**

ACU-4611-305 - ASSNET250 CAT 6 U-UTP installation cable, raw, Length 305 M, Paper Box, AWG 23/1, PVC Color grey



# **ASSNET250 Category 6 U-UTP Twisted Pair Installation Cable**

## **Performance Overview**

ASSNET Category 6 U-UTP installation cables are manufactured and tested to the ISO/IEC and DIN Standards bodies. The performance characteristics are tested up to 250 MHz including NEXT and ELFEXT as well as return loss. The performance meets the required standards, the ASSNET Installation cables are made to fulfill the high demand of applications.

# **Typical Applications**

- 1000BASE-T Gigabit Ethernet
- 100 BASE-TX Fast Ethernet

# **Physical Description**

Physical Description						
Conductor Material	Material Copper Covered Aluminum					
Conductor Diameter	0.550 +/- 0.005mm (AWG 23)					
Insulation Material	HD-PE					
Insulation Diamter	1.02 +/- 0.03mm					
Total number of insulated conductors	8 conductors, twisted in 2 x 4 pairs					
Core Color	blue x white, orange x white, green x white, brown x white					
Individual Pair Shield	none					
Overall Shield	none					
Sheath Thickness	0.55 +/- 0,05mm					
External Outer Diameter	6.3 +/- 0.3mm					
Material	PVC complied to RoHS					
Color	grey, other color's available on request					
Packing	Paper pullout box					
Carton Dimension	41.0 x 41.0 x 21.0cm					
Packing Length	305 +/- 1.5m					

# **Mechanical Properties**

Mechanical Properties					
Bend Radius	dynamic 8 x Diameter mm/min and static 4 x Diameter mm/min				
Storage Temperature	-20 to +60°C				
Installation Temperature	0 to +50°C				
Operating emerature Range	-10 to +75°C				



# **ASSNET250 Category 6 U-UTP Twisted Pair Installation Cable**

### **Technical Performance**

Technical Performance (100m)										
Frequency	RL	ATT (20°C)	NEXT	PHASE DELAY	Frequency	PS NEXT	ELFEXT	PSELFEXT		
(MHz)	>dB	<db< th=""><th>&gt;dB</th><th><ns< th=""><th>(MHz)</th><th>&gt;dB</th><th>&gt;dB</th><th>&gt;dB</th></ns<></th></db<>	>dB	<ns< th=""><th>(MHz)</th><th>&gt;dB</th><th>&gt;dB</th><th>&gt;dB</th></ns<>	(MHz)	>dB	>dB	>dB		
1	19.0	2.1	65.0	580	1	62.0	63.3	60.3		
4.0	19.0	4.0	63.0	562	4	60.5	51.2	48.2		
8.0	19.0	5.7	58.2	557	8	55.6	45.2	42.2		
10.0	19.0	6.3	56.6	555	10	54.0	43.3	40.3		
16.0	18.0	8.0	53.2	553	16	50.6	39.2	36.2		
20.0	17.5	9.0	51.6	552	20	49.0	37.2	34.2		
25.0	17.0	10.1	50.0	551	25	47.3	35.3	32.3		
31.25	16.5	11.4	48.4	550	31.25	45.7	33.4	30.4		
62.5	14.0	16.5	43.4	549	62.5	40.6	27.3	24.3		
100	12.0	21.3	39.9	548	100	37.1	23.3	20.3		
200	9.0	31.5	34.8	547	200	31.9	17.2	14.2		
250	8.0	35.9	33.1	546	250	30.2	15.3	12.3		