

S30R BATON III

RECHARGEABLE VARIABLE-OUTPUT
SIDE-SWITCH LED FLASHLIGHT

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
1050 lumens	100 days	188 meters

 Timer	 Magnetic tailcap	 Rechargeable
--	---	---

* This information is for your reference on market planning only. Please do not make it public.



S30R BATON III

RECHARGEABLE VARIABLE-OUTPUT SIDE-SWITCH LED FLASHLIGHT



MARKET APPLICATIONS:
outdoors, household

UPC: 6926540918602

DESCRIPTION

The S30R Baton III (S30R III in short) is the third generation of our flagship S30R flashlight. This flashlight includes our signature Olight blue accents with the latest Cree XM-L2 LED that covers an output range from 0.5~1,050 lumens. The S30R III is equipped with our Olight branded high performance 3500mAh 18650 rechargeable battery and USB desktop charger with suction cups on the bottom for improved stability on any surface. The S30R III is also compatible with the portable USB magnetic charging cable as an optional charging accessory (MCC) which can work with power banks for charging on the go. The high output, portability, convenient charging, and long runtime can meet all your illumination needs for home, travel, and the great outdoors.



Charging Dock (Standard)
Red: Charging
Green: Charging Completed



Red: Charging



Green: Charging Completed



MCC Magnetic Charging Cable (Optional)

S30R BATON III

RECHARGEABLE VARIABLE-OUTPUT SIDE-SWITCH LED FLASHLIGHT



FEATURES

- One customized 3500mAh 18650 battery included providing a maximum output up to 1050 lumens.
- Utilizes a smooth aluminum reflector which provides an improved beam focus for medium and close-range illumination, paired with a hardened glass lens that is coated allowing for a 99% light transmission rate.
- The S30R III is shorter by 3mm in length, reaching 114mm than the previous S30RII.
- Magnetic tail cap that allows it to be secured to ferrous metal surfaces for hands free work.
- New USB desktop charging dock provided. This flashlight has a charging port that is compatible with Olight magnetic charging cables which can be used for charging on the go.
- Low power indicator under the side switch. When the battery voltage is running low (below 3.1V), it will glow red.
- Thermal management program to protect the users' hands and flashlight from heat. The 1050 lumen turbo mode will stay on for two minutes before stepping down to the 500 lumen high mode within one minute.
- Direct access to turbo mode: when the flashlight is not under lockout mode, double click to activate the turbo mode.
- Timer function: long timer (9 minutes) and short timer (3 minutes).

OUTPUT

F1 STANDARD	MODE 1	MODE 2	MODE 3	MODE 4	MODE 5
	1050 ± 500 lumens	500 lumens	120 lumens	12 lumens	0.5 lumens
	2+200 minutes	210 minutes	15 hours	130 hours	100 days
	188 Meters				
	8,840 CD				

*Note: The test uses the provided 3500mAh 18650 rechargeable battery.

*The data above are in accordance with the ANSI NEMA FL 1-2009 standard

LIGHT SOURCE

CREE XM-L2 CW LED

DIMENSIONS

Length: 4.49 in/114mm
Diameter: 0.98 in/25mm
Weight: 3.88 oz/110g (including battery)

BODY MATERIAL

6061-T6 aluminum body with anti-scratch type-III hard anodized finish

BATTERY SOURCE

3500mAh 3.6V 18650 (Customized)

WARRANTY

5 Year warranty
Visit olightworld.com/warranty

STANDARD ACCESSORIES:

- Flashlight (with stainless steel clip)
- Customized 3500mAh 3.6V 18650 battery (included in the flashlight)
- Lanyard with Perforating Tool
- 4.2V 1000mAh Desktop Charging Dock
- 50cm Micro-USB Cable
- Instruction Manual

OPTIONAL ACCESSORIES (BUY SEPARATELY):

- Customized 3200mAh 3.6V 18650 Battery
- MCC Magnetic Charging Cable
- Pouch
- 5V 2A USB Power Supply

WATERPROOF
IPX 8



DROP TEST



COMPLIANCE



olightworld.com

All performance claims to ANSI/NEMA FL1-2009 Standard. Made in China.

© Olight 10/28/16 V1