

KERN KFP 600V20NM

Wägebrücke aus rutschfestem Stahl-Riffelblech, lackiert mit IP67



Construction

Cable length:	5 m
Dimensions of weighing plate (WxDxH):	1500 x 1250 x 80 mm
Material weighing plate:	Steel lacquered
Revolving screw feet:	yes
Weighing surface (WxD):	1500 x 1250 mm

Measuring system

Readout [d]:	200 g
Resolution (non verifiable):	3000
Weighing range [Max]:	600 kg

Technical data about verification

Minimum load [Min]:	4 kg
Periodic Verification for Italy:	969-112
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	200 g

Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Service

Adjustment at the location of installation:	961-250
DAkkS Certificate:	963-130
Verification:	965-230

Category

Brand:	KERN
Category:	Platforms
Product Group:	Weighing bridge

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1550 x 1300 x 260 mm
Gross weight:	165 kg
Net weight:	135 kg
Shipping method:	Freight forwarder