

KERN KXS-TM

Auswertegerät aus Edelstahl mit Schutzgrad IP68 und integriertem Netzteil



Measuring system

Adjustment options:	External calibration
Number of weighing ranges:	2
Resolution (non verifiable):	30000
Resolution (verifiable):	10000
Weighing units:	g kg

Display

Display digit height:	5,500 cm
-----------------------	----------

Technical data about verification

Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III

Functions

Counting function:	yes
Data hold function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	EURO
Operating time (Backlight off):	80 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional - intern

Service

Adjustment at the location of installation: auf Anfrage | on request

Category

Brand:	KERN
Category:	Display devices
Product Group:	Display device

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	325 x 245 x 205 mm
Gross weight:	3,200 kg
Net weight:	2,500 kg
Shipping method:	Parcel service

Construction

Casing material:	stainless steel
Dimensions housing (WxDxH):	232 x 170 x 80 mm
Wall mount:	yes