

# KERN MWA 300K-1M



Rollstuhlwaage mit zwei integrierten Auffahrampen für bequemes Auffahren â mit Eich- und Medizinzulassung für den professionellen Einsatz in der medizinischen Diagnostik



## Measuring system

Adjustment options:	External calibration
Linearity:	100 g
Readout [d]:	100 g
Recommended adjusting weight:	300 kg (M1)
Reproducibility:	100 g
Resolution:	3000
Tare range:	-299900000 mg
Warm up time:	10 min
Weighing range [Max]:	300 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	2,500 cm
Display digit height:	5 mm

## Technical data about verification

Minimum load [Min]:	2 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	100 g

## Functions

BMI function:	yes
Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	5 %

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	20 h
Operating time (Backlight off):	40 h
Operating time (Backlight on):	20 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-129

## Category

Brand:	KERN
Category:	Balances
Product Group:	Wheelchair platform scale

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1255 x 1100 x 285 mm
Gross weight:	69,200 kg
Net weight:	72 kg
Shipping method:	Freight forwarder

## Construction

Cable length of display device:	3 m
Casing material:	Steel lacquered
Dimensions of display device (WxDxH):	200 x 55 x 128 mm
Dimensions of weighing plate (WxDxH):	1190 x 1140 x 80 mm

# KERN MWA 300K-1M



Rollstuhlwaage mit zwei integrierten Auffahrampen für bequemes Auffahren â mit Eich- und Medizinzulassung für den professionellen Einsatz in der medizinischen Diagnostik

of stand:	94 cm
Level indicator:	yes
Material weighing plate:	Steel lacquered
Overall dimensions mounted (WxDxH):	1190 x 1140 x 80 mm
Wall mount:	yes
Weighing surface (WxD):	880 x 840 mm