

KERN CCS3T-1

Zählsystem zum Zählen kleinster Teile in großen Mengen, Zählauflösung bis zu 999.999 Punkte



Service

Adjustment at the location of installation: abhängig von
Auflösung/Max | depends
on resolution and capacity

DAkkS Certificate: 962-132-128

Category

Brand: KERN

Product Group: Counting system

Packaging & shipping

Delivery: 120 h

Dimensions packaging (WxDxH): 1525 x 1275 x 235 mm

Gross weight: 185 kg

Net weight: 180 kg

Shipping method: Freight forwarder

Construction

Cable length of display device: 2,500 m

Casing material: Plastic

Dimensions of weighing plate
(WxDxH): 1500 x 1250 x 80 mm

Level indicator: yes

Material weighing plate: Metal lacquered

Overall dimensions mounted
(WxDxH): 320 x 330 x 125 mm

Revolving screw feet: yes

Weighing surface (WxD): 1500 x 1250 mm

Measuring system

Adjustment options: External calibration

Linearity: 500 mg

Recommended adjusting weight: 3000 kg (M1)

Reproducibility: 200 mg

Weighing system: Strain gauge

Weighing units: kg lb

Display

Display digit height: 2 cm

Counting

Counting resolution: 30000000

Minimum piece weight at piece
counting (Laboratory): 100 mg

Minimum piece weight at piece
counting (Normal): 1 g

Reference weight: yes

Functions

Conversion function: yes

Counting function: yes

Function to save totals: yes

PRE-TARE function: yes

Weighing with tolerance range: yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: 0 °C

Minimum humidity: 0 %

Power supply

Charging time: 12 h

Input voltage: 220 V - 240 V AC 50 Hz

n/a: CH EURO UK

Operating time (Backlight on): 70 h

Rechargeable battery: Rchrg. battery optional