

KERN KFD 1500V40M

Wägebrücke

KERN[®]

Material weighing plate:	stainless steel
Weighing surface (WxD):	1600 x 1200 mm



Measuring system

Readout [d]:	500 g
Resolution (non verifiable):	3000
Weighing range [Max]:	1,500 t

Technical data about verification

Minimum load [Min]:	10 kg
Verification by KERN possible:	yes
Verification value [e]:	500 g

Service

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130
Verification:	965-230

Category

Brand:	KERN
Category:	Platforms
Product Group:	Weighing bridge

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1650 x 1250 x 350 mm
Gross weight:	150 kg
Net weight:	130 kg
Shipping method:	Freight forwarder

Construction

Cable length:	5 m
Cable length of display device:	5 m
Dimensions of weighing plate (WxDxH):	1600 x 1200 x 78 mm