

# KERN KFP 600V40SM

Edelstahl-Plattform mit IP68-Schutz

Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	1000 x 1000 mm



## Measuring system

Readout [d]:	200 g
Resolution (non verifiable):	3000
Weighing range [Max]:	600 kg

## Technical data about verification

Minimum load [Min]:	4 kg
Verification value [e]:	200 g

## Service

Adjustment at the location of installation: abhängig von  
Auflösung/Max | depends  
on resolution and capacity

DAkkS Certificate:	963-130
--------------------	---------

## Category

Brand:	KERN
Category:	Platforms
Product Group:	Weighing bridge

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1150 x 1150 x 350 mm
Gross weight:	116 kg
Net weight:	95 kg
Shipping method:	Freight forwarder

## Construction

Cable length:	5 m
Dimensions of weighing plate (WxDxH):	1000 x 1000 x 80 mm