

# KERN BFB6T-3M

Robuste Bodenwaage mit Eichzulassung [M] - bis 6 t



## Measuring system

Adjustment options:	External calibration
Linearity:	2 kg
Readout [d]:	2 kg
Recommended adjusting weight:	6000 kg (M2)
Reproducibility:	2 kg
Resolution:	3000
Stabilisation time:	2 s
Tare range:	-3000000000 mg
Warm up time:	10 min
Weighing range [Max]:	6 t
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	5,200 cm
-----------------------	----------

## Technical data about verification

Minimum load [Min]:	40 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	2 kg

## Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

## Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)

## Service

Adjustment at the location of installation:	961-252
DAkkS Certificate:	963-132
Verification:	965-232

## Category

Brand:	KERN
Category:	Balances
Product Group:	Floor scale

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1550 x 1550 x 345 mm
Gross weight:	280 kg
Net weight:	210 kg
Shipping method:	Freight forwarder

## Construction

Cable length of display device:	5 m
Dimensions housing (WxDxH):	250 x 160 x 58 mm
Dimensions of display device (WxDxH):	250 x 160 x 58 mm
Dimensions of weighing plate (WxDxH):	1500 x 1500 x 130 mm
Level indicator:	yes
Material weighing plate:	Steel lacquered
Revolving screw feet:	yes
Weighing surface (WxD):	1500 x 1500 mm