


KERN BIC600K-1

Hochauflösende Bodenwaage mit 2x3000 [d] und top Preis-Leistungs-Verhältnis



Service

Adjustment at the location of installation: 961-250

DAkkS Certificate: 963-130

Category

Brand: KERN

Category: Balances

Product Group: Floor scale

Packaging & shipping

Delivery: 48 h

Dimensions packaging (WxDxH): 1050 x 1050 x 260 mm

Gross weight: 180 kg

Net weight: 150 kg

Shipping method: Freight forwarder

Construction

Cable length: 5 m

Cable length of display device: 5 m

Dimensions (WxDxH): 1200 x 1500 x 108 mm

Dimensions of display device (WxDxH): 235 x 114 x 51 mm

Dimensions of weighing plate (WxDxH): 1200 x 1500 x 108 mm

Level indicator: yes

Revolving screw feet: yes

Weighing surface (WxD): 1200 x 1500 mm

Measuring system

Adjustment options: External calibration

Linearity: 300 g | 600 g

Readout [d]: 100 g | 200 g

Recommended adjusting weight: 600 kg (M2)

Reproducibility: 100 g | 200 g

Resolution: 3 3.000

Stabilisation time: 2 s

Tare range: -600000000 mg

Warm up time: 10 min | 10 min

Weighing range [Max]: 300 kg | 600 kg

Weighing system: Strain gauge

Weighing units: g kg lb oz

Display

Display digit height: 2,500 cm

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: -10 °C

Minimum humidity: 0 %

Power supply

Input voltage: 100 V - 240V AC 50/60Hz
0.3A

n/a: AUS EURO UK US

n/a: Mains adapter external

Power supply

Operating time: 60 h