

KERN BXS3T-3M



Wägebrücke mit verschraubter Wägeplatte (IP67) und Edelstahl-Auswertegerät (IP68), mit Eichzulassung [M]



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	EURO
Operating time (Backlight off):	80 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rechrg. battery optional (factory)

Service

Adjustment at the location of installation:	961-252
DAkkS Certificate:	963-132
Verification:	965-232

Category

Brand:	KERN
Category:	Balances
Product Group:	Floor scale

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1530 x 1300 x 335 mm
Gross weight:	174 kg
Net weight:	145 kg
Shipping method:	Freight forwarder

Construction

Cable length of display device:	5 m
Dimensions of display device (WxDxH):	232 x 170 x 80 mm
Dimensions of weighing plate (WxDxH):	1500 x 1250 x 80 mm
Level indicator:	yes
Material weighing plate:	Steel lacquered
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	1500 x 1250 mm

Measuring system

Adjustment options:	External calibration
Linearity:	1 kg
Readout [d]:	1 kg
Recommended adjusting weight:	3000 kg (M2)
Reproducibility:	1 kg
Resolution:	3000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	3 t
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	5,500 cm
-----------------------	----------

Technical data about verification

Minimum load [Min]:	20 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	1 kg

Functions

Counting function:	yes
Data hold function:	yes
Function to save totals:	yes
Peak function:	yes
PRE-TARE function:	yes
Standby function:	yes
Weighing with tolerance range:	yes