


KERN EWJ6000-1M

Hochwertige Präzisionswaage mit interner Justierautomatik und Eichzulassung [M]



Minimum piece weight at piece counting (Normal): 200 mg

Functions

Capacity display:	yes
Counting function:	yes
Percentage determination:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	15 °C

Power supply

Charging time:	4 h
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	15 h
Operating time (Backlight on):	10 h
Rechargeable battery:	Rchrg. battery optional - intern

Service

DAkkS Certificate:	963-128
Verification:	965-217

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	390 x 285 x 270 mm
Gross weight:	4,350 kg
Net weight:	3,400 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	215 x 330 x 105 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	155 x 145 mm

Measuring system

Adjustment options:	Internal calibration (auto)
Linearity:	300 mg
n/a:	200 g
Readout [d]:	100 mg
Recommended adjusting weight:	6 kg (F1)
Reproducibility:	100 mg
Resolution:	60000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	6 kg
Weighing system:	Strain gauge
Weighing units:	g

Display

Display digit height:	1,650 cm
-----------------------	----------

Technical data about verification

Minimum load [Min]:	5 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	II
Verification value [e]:	1 g

Counting

Counting resolution:	300000
Minimum piece weight at piece counting (Laboratory):	20 mg