

KERN FOB 30K-3NL



Edelstahl-Tischwaage mit großem Wägebereich und hohem Schutzgrad IP67 gegen Staub und Spritzwasser



Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	415 x 305 x 165 mm
Gross weight:	4,550 kg
Net weight:	3,750 kg
Shipping method:	Parcel service

Construction

Casing material:	stainless steel
Dimensions housing (WxDxH):	285 x 255 x 90 mm
Dimensions of weighing plate (WxDxH):	252 x 200 x 14 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	252 x 200 mm

Measuring system

Adjustment options:	External calibration
Linearity:	6 g 15 g
Readout [d]:	2 g 5 g
Recommended adjusting weight:	30 kg (M1)
Reproducibility:	2 g 5 g
Resolution:	8 6.000
Stabilisation time:	2 s
Warm up time:	30 min 30 min
Weighing range [Max]:	16 kg 30 kg
Weighing system:	Strain gauge
Weighing units:	g lb oz

Display

Display digit height:	2,500 cm
-----------------------	----------

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C
Minimum humidity:	25 %

Power supply

Input voltage:	230 V AC 50 Hz
----------------	----------------

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	48 h
-----------------	------

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
--------------------	---------