

KERN GAT10K-4

KERN Easy-Touch-Tischwaage à die intuitive Art zu Wiegen



Functions

Capacity display:	yes
Counting function:	yes
Function to save totals:	yes
Help function on the display:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Time display:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK US

n/a: Mains adapter external

Power supply

Operating time (Backlight on):	10 h
Rechargeable battery:	Rchrg. battery optional - intern

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	475 x 360 x 200 mm
Gross weight:	3,800 kg
Net weight:	3 kg
Shipping method:	Parcel service

Measuring system

Adjustment options:	External calibration
Linearisation (points):	2
Linearity:	1,500 g
Readout [d]:	500 mg
Recommended adjusting weight:	15 kg (F2)
Reproducibility:	500 mg
Resolution:	30000
Stabilisation time:	2 s
Tare range:	-15000000 mg
Warm up time:	2 h
Weighing range [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	g kg lb oz t

Display

Display digit height:	1,200 cm
Display digit height:	1,200 cm

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	500 mg
Minimum piece weight at piece counting (Normal):	5 g
Reference weight:	yes

KERN GAT10K-4



KERN Easy-Touch-Tischwaage à die intuitive Art zu Wiegen

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	315 x 350 x 120 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	315 x 350 x 120 mm
Revolving screw feet:	yes
Weighing surface (WxD):	300 x 225 mm