

# KERN HFA1T-4

Kompakte Kranwaage mit integrierter Anzeige, auch für Zugkraftmessungen verwendbar



## Measuring system

Adjustment options:	External calibration
Linearity:	1 kg
Precision (of [Max]):	0,002
Readout [d]:	500 g
Recommended adjusting weight:	1000 kg (M3)
Reproducibility:	500 g
Resolution:	2000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	1 t
Weighing system:	Strain gauge
Weighing units:	kg lb N

## Display

Display digit height:	2,300 cm
Display digit height:	2 mm

## Functions

Data hold function:	yes
---------------------	-----

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	40 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

## Service

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130H
--------------------	----------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 330 x 130 mm
Gross weight:	2,500 kg
Net weight:	1,800 kg
Shipping method:	Parcel service
UN number:	3496

## Construction

Casing material:	aluminium
Dimensions housing (WxDxH):	90 x 55 x 255 mm