

KERN HFO3T1M

Industrie-Kranwaage bis 10 Tonnen â jetzt auch mit Eichzulassung [M]



Measuring system

Adjustment options:	External calibration
Linearity:	1 kg
Precision (of [Max]):	0,002
Readout [d]:	1 kg
Recommended adjusting weight:	3000 kg (M1)
Reproducibility:	1 kg
Resolution:	3000
Stabilisation time:	2 s
Tare range:	-2999000000 mg
Warm up time:	10 min
Weighing range [Max]:	3 t
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	3 cm
-----------------------	------

Technical data about verification

Minimum load [Min]:	20 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	1 kg

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	14 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight on):	50 h
--------------------------------	------

KERN HFO3T1M

Industrie-Kranwaage bis 10 Tonnen â jetzt auch mit Eichzulassung [M]



Service

Adjustment at the location of installation: 961-252

DAkkS Certificate: 963-132H

Verification: 965-132H

Category

Brand: KERN

Category: Balances

Product Group: Crane scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 370 x 545 x 340 mm

Gross weight: 18 kg

Net weight: 16,500 kg

Shipping method: Parcel service

UN number: 2800

Construction

Casing material: cast iron

Dimensions of display device
(WxDxH): 270 x 175 x 200 mm