

KERN KFB-TM

Auswertegerät mit großen, bequem ablesbaren Ziffern



Measuring system

Adjustment options:	External calibration
Linearisation (points):	3
Number of weighing ranges:	2
Resolution (non verifiable):	30000
Resolution (verifiable):	6000
Weighing units:	kg lb

Display

Display digit height:	5,200 cm
-----------------------	----------

Technical data about verification

Verification approval conforming to 2014/31/EU:	yes
Verification class:	III

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional

Service

Adjustment at the location of installation: auf Anfrage | on request

Category

Brand:	KERN
Category:	Display devices
Product Group:	Display device

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	330 x 200 x 220 mm
Gross weight:	1,730 kg
Net weight:	1,060 kg
Shipping method:	Parcel service

Construction

Dimensions housing (WxDxH):	250 x 160 x 65 mm
Dimensions of display device (WxDxH):	250 x 160 x 65 mm