

KERN KFP 300V30M

Edelstahl-Plattform



Measuring system

Readout [d]:	10 g
Resolution (non verifiable):	30000
Weighing range [Max]:	300 kg

Technical data about verification

Minimum load [Min]:	2 kg
Verification by KERN possible:	yes
Verification value [e]:	100 g

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	740 x 580 x 230 mm
Gross weight:	25 kg
Net weight:	22 kg
Shipping method:	Parcel service

Construction

Cable length:	2,500 m
Dimensions of weighing plate (WxDxH):	650 x 500 x 135 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	650 x 500 mm