

KERN KFP 30V30SM

Edelstahl-Plattform



Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	300 x 240 mm

Measuring system

Readout [d]:	10 g
Resolution (non verifiable):	30000
Weighing range [Max]:	30 kg

Technical data about verification

Minimum load [Min]:	200 g
Verification by KERN possible:	yes
Verification value [e]:	10 g

Environmental conditions

Maximum operating temperature:	40 °C
--------------------------------	-------

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
Verification:	965-228

Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 360 x 240 mm
Gross weight:	8 kg
Net weight:	5 kg
Shipping method:	Parcel service

Construction

Cable length:	2,500 m
Dimensions of weighing plate (WxDxH):	300 x 240 x 100 mm