

# KERN KXP6V20LM

Edelstahl-Wägeplatte

**KERN**<sup>®</sup>



## Measuring system

Readout [d]:	200 mg
Resolution (non verifiable):	30000
Weighing range [Max]:	6 kg

## Technical data about verification

Minimum load [Min]:	40 g
Verification by KERN possible:	yes
Verification value [e]:	1 g   2 g

## Service

Adjustment at the location of installation:	961-248
DAkkS Certificate:	963-128
Verification:	965-228

## Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	395 x 350 x 230 mm
Gross weight:	4 kg
Net weight:	3,200 kg
Shipping method:	Parcel service

## Construction

Cable length:	3 m
Dimensions of weighing plate (WxDxH):	300 x 240 x 90 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	300 x 240 mm