

# KERN CCS6K-6

Zählsystem zum Zählen kleinster Teile in großen Mengen, Zählauflösung bis zu 999.999 Punkte



## Measuring system

Adjustment options:	External calibration
Linearity:	5 mg
Recommended adjusting weight:	300 g (F1)
Reproducibility:	2 mg
Weighing system:	Strain gauge
Weighing units:	g

## Display

Display digit height:	2 cm
-----------------------	------

## Counting

Counting resolution:	1200000
Minimum piece weight at piece counting (Laboratory):	5 mg
Minimum piece weight at piece counting (Normal):	50 mg
Reference weight:	yes

## Functions

Conversion function:	yes
Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

## Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	60 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional

## Service

Adjustment at the location of installation: abhängig von Auflösung/Max | depends on resolution and capacity

DAkkS Certificate:	962-128-127
--------------------	-------------

## Category

Brand:	KERN
Product Group:	Counting system

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	550 x 235 x 80 mm
Gross weight:	7 kg
Net weight:	3,800 kg
Shipping method:	Parcel service

## Construction

Cable length:	1,500 m
Cable length of display device:	2,500 m
Casing material:	Plastic
Dimensions of weighing plate (WxDxH):	230 x 230 x 100 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 330 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	230 x 230 mm